



TYPICAL BASELINE OHMIC VALUES (ON FLOAT)

BATTERY TYPE	BASELINE OHMIC VALUES ON FLOAT			
	MIDTRONICS** (SIEMEN'S)	ALBER CELLCORDER (MILLI-OHMS)	BIDDLE BITE 2 (MILLI-OHMS)	BIDDLE MBITE (MILLI-OHMS)
U1HR1500	747	8.848	7.238	7.876
45HR2000	925	7.153	5.852	6.368
24HR3000	1319	5.014	4.102	4.464
27HR3500	1567	4.220	3.452	3.756
31HR4000	1926	3.433	2.808	3.056
31HR5000	1487	4.448	3.639	3.959
4DHR6500	2222	2.976	2.435	2.649
HR3500ET	1759	3.758	3.040	3.294
HR5500ET	2080	3.177	2.570	2.784
HR7500ET	2460	2.666	2.156	2.337

- The above data are typical results and do not form a specification.
- Values are subject to change without notification.
- These values are not to be used to determine warranty claims.

** - Midtronics Meters include:
 Micro Celltron CTM-100
 Celltron Advance CTA-2000
 Celltron Ultra CTU-6000

Suspect ohmic values should be confirmed with a discharge test to determine the true capacity. Reference values stored in an ohmic meter must agree with the above tables for best results. Testers with pass/fail modes must use algorithms based on these reference values; although, a more thorough method of testing is recommended.

"POWERED FOR PERFORMANCE"®

DISTRIBUTED BY:

EAST PENN manufacturing co., inc.

Lyon Station, PA 19536-0147 • Phone: 610-682-6361 • Fax: 610-682-4781

Order Department Hotline: 610-682-4231

www.eastpennunigy.com • e-mail: sales@eastpennunigy.com

E.P.M. Form No. 0739 3/11

© 2011 by EPM Printed in U.S.A.

All data subject to change without notice.
 No part of this document may be copied or reproduced, electronically or mechanically, without written permission from the company.